



Presented With Compliments From
www.DirectHomeMedical.com

PHILIPS
RESPIRONICS

DreamStation Go

Portable PAP
therapy system



Rediscover dreams



© 2017 Koninklijke Philips N.V. All rights reserved.
Specifications are subject to change without notice.

www.philips.com/respironics

Caution: US federal law restricts these devices to
sale by or on the order of a physician.

RRDPGH EB 3/1/17 PN 1133355 MCI 4107883
1010 Murry Ridge Lane, Murrysville, PA 15668
800-345-6443 • 724-387-4000

Convenience without compromise



The **DreamStation Go** is a compact and highly portable PAP system designed for patients who refuse to compromise.



Travel



Second residence



Easy-to-use device



Powerful, portable, performance

At half the size of our System One and DreamStation platforms, DreamStation Go offers the same therapy and comfort features used by more than 5 million CPAP users.



DreamMapper cross-device connectivity

Users of DreamMapper, our patient self-management tool, can sync data from multiple DreamMapper-enabled devices* to one account. Users have the ability to track and monitor their combined progress across both home and portable PAP devices in one convenient dashboard on their smartphone, tablet, or computer.

Micro-flexible tubing

DreamStation Go features the smallest PAP tubing we've ever offered. Engineered to minimize bulk and improve mobility, our 12mm tubing is 58% smaller than our 22mm performance tubing. It offers enhanced flexibility, portability, and connectivity.

- The click-connect PAP-side cuff simplifies connection of the mask tube to the PAP.
- The click-connect mask-side cuff streamlines the connection point and is easy on hands.



*To see which therapy devices are compatible with DreamMapper, visit www.dreammapper.com/compatible.

Innovation for people on the go

DreamStation Go provides the portability and packability travelers want and the effective therapy they need.

**65%
smaller***

The DreamStation Go is 65% smaller than ResMed's AirSense 10 and AirStart 10.

**48%
lighter***

The DreamStation Go is 48% lighter than ResMed's AirSense 10 and AirStart 10.

**33%
fewer components****

The DreamStation Go requires 33% fewer components to pack than its closest competitors.

*2016 internal measurement of ResMed's AirSense 10 and AirStart 10 with side cover installed. Includes power supply. Data on file.

**When compared to HDM Z1 and Somnetics Transcend devices, (2016).

Powerfully convenient features



Built-in power supply reduces the number of parts managed by the patient for added convenience.



Intuitive color touchscreen offers quick, simple setup and easy navigation.



MicroSD card stores compliance and waveform data.*



Onboard USB port allows for easy charging of mobile devices.



Bluetooth is standard with every device.



Complies with FAA requirements for in-flight use.**



Device is compatible with our DreamMapper patient self-management tool.

12mm tube

Our new-to-market 12mm micro-flexible tubing is our smallest and lightest ever.



Click-connect

Click-connections on each end of the micro-flexible tubing make connecting and disconnecting the device and mask simple.

*Sold separately.
**RTCA/DO-160G section 21, category M.

Accessories create a world of opportunities



Overnight battery
Compact and lightweight with a recharge time of just 4-5 hours.



Small travel kit
Kit includes an easy-to-pack protective case for the DreamStation Go and a separate, washable bag for the mask and tube.



Medium travel kit
Kit includes a protective case that accommodates the DreamStation Go and overnight battery. Also includes separate, washable bag for the mask and tube.



Air filters
Your choice of a reusable pollen or disposable 30-day fine filter.



DreamStation Go Auto specifications

Pressure range	4 to 20 cm H ₂ O
Pressure mode(s)	CPAP, APAP
Flex pressure relief	1 to 3
Flex modes	C-Flex, C-Flex+, A-Flex
Ramp time	0 to 45 min (5-min increments)
Starting ramp pressure	Patient adjustable, Smart Ramp
Dimensions	15 cm L x 15 cm W x 5.8 cm H
Weight	844 g (1.86 lb.)
Filters	Reusable pollen, combination fine
Device setup	Touchscreen color display
Data storage capacity	On-board: > 1 year MicroSD card (optional): lifetime
Compliance meter	Breathing detection
Altitude compensation	Automatic
Electrical requirements	100-240 VAC, 50/60 Hz
Warranty	Two years

Ordering information

Flow Generators	Part number
DreamStation Go CPAP	DSG400S11
DreamStation Go Auto CPAP	DSG500S11
Power	Part number
DreamStation Go overnight battery	1133281
Travel kits	Part number
DreamStation Go small travel kit*	1133275
DreamStation Go medium travel kit**	1133276
Consumables/Replacement	Part number
DreamStation micro-flexible 12mm tubing	PR12
Power cord 6ft white	1132551
Power cord 10ft white	1132552
Beauty panel - front	1133741
Beauty panel - rear	1133742
Reusable pollen filter 2-pk	1133743
Disposable 30-day fine filter 6-pk	1133744

DreamStation Go CPAP specifications

Pressure range	4 to 20 cm H ₂ O
Pressure mode(s)	CPAP
Flex pressure relief	1 to 3
Flex modes	C-Flex, C-Flex+
Ramp time	0 to 45 min (5-min increments)
Starting ramp pressure	Patient adjustable, Smart Ramp
Dimensions	15 cm L x 15 cm W x 5.8 cm H
Weight	844 g (1.86 lb.)
Filters	Reusable pollen, combination fine
Device setup	Touchscreen color display
Data storage capacity	On-board: > 1 year MicroSD card (optional): lifetime
Compliance meter	Breathing detection
Altitude compensation	Automatic
Electrical requirements	100-240 VAC, 50/60 Hz
Warranty	Two years

Learn more

For more information about DreamStation Go, visit www.philips.com/dreamstationgo.

*Small travel kit includes an easy-to-pack protective case for the DreamStation Go and a separate washable mask and tube bag.

**Medium travel kit includes a protective case that accommodates the DreamStation Go and overnight battery. Also includes a separate washable mask and tube bag.